



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
e	0.40 BSC		
N	48		
ND	12		
L	0.30	0.40	0.50
b	0.15	0.20	0.25
D2	4.40	4.50	4.60
E2	4.40	4.50	4.60
D	6.00 BSC		
E	6.00 BSC		
A	-	-	0.90
A1	0.00	-	0.05
A3	0.203 REF		
K	0.35 MIN		

#### NOTES:

- ALL DIMENSIONS ARE IN MILLIMETERS.
- N IS THE TOTAL NUMBER OF TERMINALS.
- 3** DIMENSION "b" APPLIES TO METALLIZED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.30mm FROM TERMINAL TIP. IF THE TERMINAL HAS THE OPTIONAL RADIUS ON THE OTHER END OF THE TERMINAL, THE DIMENSION "b" SHOULD NOT BE MEASURED IN THAT RADIUS AREA.
- 4** ND REFERS TO THE NUMBER OF TERMINALS ON D SIDE.
- 5** PIN #1 ID ON TOP WILL BE LOCATED WITHIN THE INDICATED ZONE.
- 6** COPLANARITY ZONE APPLIES TO THE EXPOSED HEAT SINK SLUG AS WELL AS THE TERMINALS.
- JEDEC SPECIFICATION NO. REF. : N/A.